KIMTECH

Kimtech™ G3 Latex Gloves

Kimtech™ G3 Latex Gloves provide enhanced tactile sensitivity and performance, combined with high contamination control, for seamless protection when and where it counts.

During manufacture the natural rubber latex gloves are washed repeatedly in ultrapure deionised water to ensure consistent control of particles and extractables. Gloves are then double-bagged with polyethylene materials and case liner to maintain cleanliness.

The ambidextrous gloves are non-sterile and are recommended for ISO Class 3 or higher cleanroom environments, providing enhanced wearer protection and handling performance for even the most challenging applications. A high-quality finish with texturing on the palm and fingertips provides improved grip, tactile sensitivity and comfort in both wet and dry conditions.

In addition, the powder-free construction minimises contamination and drying effects on the wearer's skin, ensuring that cleanroom users are protected as much as their processes and equipment.

The disposable gloves feature beaded cuffs for easy donning and better seal formation with other garments. Rigorous product development, testing and proven manufacturing processes results in latex cleanroom gloves that satisfy regulatory compliance requirements.

Double bagged with case liner

- Enhanced tactile sensitivity
- Excellent cleanliness level
- Textured finish for enhanced grip





Cleanliness characteristics

Cleanliness characteristics	Limit		Test	
			method	
Particles				
Per cm²≽ 0,5µm	1500			
Extractables	μg/g	μg/cm²		
Sodium (Na+)	25	0.16		
Ammonium (NH ₄ +)	10	0.07]	
Potassium (K+)	5	0.03	IEST-RP-	
Magnesium (Mg²+)	5	0.03	CC005	
Calcium (Ca²+)	20	0.13		
Chloride (Cl ⁻)	100	0.67		
Nitrate (NO ³⁻)	15	0.10		
Sulfate (SO ₄ ²⁻)	25	0.17		
Zinc (Zn²+)	90	0.60		

Size Guide

Size	Former Code	New Code	Length	Quantity
S	HC225	56813	30.5 cm	100 gloves / bag = 1,000 gloves
М	HC335	56814		
	HC445	56815		
XL	HC555	56816		

Kimtech™ G3 Latex Gloves

Key Features

- > High quality natural rubber latex¹ material provides high levels of protection against micro-organisms and chemical splash
- > Washed repeatedly in ultrapure deionised water resulting in low levels of particles and extractables
- > Beaded cuffs add strength to the gloves, reducing the risk of tearing and increasing their durability, while also reducing roll down for easier donning and doffing

Assured Compliance

- > PPE Cat III according to Regulation (EU) 2016/425 and to the Regulation 2016/425 as brought into the UK law and amended
- > EN ISO 374-1 Type C Chemical Splash protection
- > EN 374-4 Resistance to degradation by chemicals
- > EN ISO 374-5 Micro-organism and VIRUS Protection

Quality Standards

- > Manufactured in accordance with Quality System ISO 9001 and ISO 13485
- > Certificate of analysis (CoA) available online for each production lot at www.kimtech.eu

Packaging Configuration

- > 1,000 gloves per case = 100 gloves per double polybag; x10 polybags per case liner
- > Packaged in ISO Class 5 Cleanroom

Product Specifications

Characteristics	Value				Test method
Freedom from holes	AQL 1.5 ²				EN 374-2 ASTM D5151
Tensile properties	Tensile strength		Ultimate elongation		
Before aging	28 MPa, nominal		845%, nominal		ASTM D412 ASTM D3578
After accelerated aging	27 MPa, nominal 895%, nominal		ASTM D5778 ASTM D573		
Dimension	Nominal thickness/width				
Thickness (mm)	Middle finger	Palm Cuff		EN 21420	
,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,	0.22	0.22 0.20 0.15			
Palm width (mm)	S	М	L	XL	ASTM D3578
Patifi width (min)	85	96	109	118	
Particles (Maximum)					
Per cm² ≥ 0.5 μm	<1500			IEST-RP-CC005	
Protein (residual content)					
µg/g	50				ASTM D6124







CE 0123 器 0168

Visit us at www.kimtech.eu or for any questions, email: kimtech.support@kcc.com

¹CAUTION: This product contains natural rubber latex which may cause allergic reactions.

² AQL as defined per ISO 2859-1 for sampling by attributes.



